



## Multiple-Connectors Administering via i.v. access



EN040

- **Neo-Link Multiple-connectors**
- Easy-to-handle, simply and effective disinfecting
- Protection against injuries from needle pricks and against infections
- No protective cap required
- Suitable for long term infusions up to 96h

- Safe application of e.g. high concentrated solutions or catecholamines
- Special design from 2 feeds up to 8 feeds connector
- Free of DEHP and latex



- **Check-valve connectors**
- Ensure constant pressure at the parallel infusion
- Preventing uncontrolled mixing of solutions
- Faster pump alarm when a line become blocked
- Inline-filter integrated on demand
- Depending on appliance also available in different tube diameter or in light-shielded lines



SN1064F


## Multiple-Connectors Administering via i.v. access

Code No.	Description	Prime	Material <sup>1)</sup>	Specifics <sup>2)</sup>	Pack unit
	<b>Neo-Link Multiple-Connectors <sup>3)</sup></b>	<b>ml</b>			
<b>EN020</b>	Connector PUL with Neo-Link	0,5	PUL	Y	50
<b>EN030</b>	3-way Connector PUL with Neo-Link	0,8	PUL	3-Y	50
<b>EN040</b>	4-way Connector PUL with Neo-Link	0,9	PUL	4-Y	50
<b>EN060</b>	6-way Connector PUL with Neo-Link	1,4	PUL	6-Y	50
<b>EN080</b>	6-way Connector PUL with Neo-Link	1,7	PUL	8-Y	50
	<b>Check-valve Connectors <sup>3)</sup></b>				
<b>SN1052</b>	2-way check valve connector, large	1,0	ND 3mm	Y, RV	50
<b>SN1053</b>	3-way check valve connector, large	1,7	ND 3mm	3-Y, RV	50
<b>SN1054</b>	4-way check valve connector, large	2,4	ND 3mm	4-Y, RV	50
<b>SN1062</b>	2-way check valve connector, small	0,5	ND	Y, RV	50
<b>SN1062F</b>	2-way check valve con., 0.2µm pos. filter	0,8	ND	Y, RV	50
<b>SN1062G</b>	2-way check valve connector, light-shielded	0,4	PE / ND	Y, RV	50
<b>SN1063</b>	3-way check valve connector, small	0,8	ND	3-Y, RV	50
<b>SN1063F</b>	3-way check valve con., 0.2µm pos. filter	1,1	ND	3-Y, RV	50
<b>SN1063G</b>	3-way check valve connector, light-shielded	0,7	PE / ND	3-Y, RV	50
<b>SN1064</b>	4-way check valve connector, small	0,9	ND	4-Y, RV	50
<b>SN1064F</b>	4-way check valve con., 0.2µm pos. filter	1,2	ND	4-Y, RV	50
<b>SN1064G</b>	4-way check valve connector, light-shielded	0,8	PE / ND	4-Y, RV	50
<b>SN1082</b>	2-way check valve con., 1.2µm filter	1,0	ND	Y, RV	50
<b>SN1082L</b>	CV-Set for Baxter /Ivac-Pumps, 1,2µm filter	1,1	ND	Y, RV	50
<b>SN1083</b>	3-way check valve con., 1.2µm filter	1,3	ND	3-Y, RV	50
<b>SN1084</b>	4-way check valve con., 1.2µm filter	1,4	ND	4-Y, RV	50

<sup>1)</sup> Tube material: ND – DEHP-free PVC / PE – Polyethylene / PU m – Polyurethane micro-vol. / PUL – Polyurethane low-volume

<sup>2)</sup> Specifics: P – Injection port / RV – check valve / K – clamp / Sw – Swivel-Luer-Lock / Y – Y-junction

<sup>3)</sup> In some extent with permanent venting micro infusion filter in the named pore size



**SN1052**  
Check-valve connector,  
large



**SN1064**

**EN020**  
Connector PUL with Neo-Link

